JANOME MC9450 QCP



Horizon Memory Craft 9450 QCP

The MC9450 QCP has all the features you require to go ahead and get creative whether you are a dressmaker a quilter or simply love sewing.

The large LCD color touch screen makes it so easy to use.

You have the ability to customize each stitch including buttonholes and save them as a favourite stitch. Sewing Applications gives you a variety of pre-set stitch functions, ready to sew zips, blind hem, buttons, quilting, ruler work, patchwork and lots more.



Brighter LED lights

The LED lights on the MC9450 QCP are approximately 1.6 times brighter than the MC9400 QCP

9 LED lights in total


3 in the throat area and 6 in the needle area.



Auto-power off timer

Default setting :-7 hours with a time range of 1-12 hours It can also be turned OFF if required.






Default setting

7 hours

Tapering capability (1)

You can select stitches from Tapering category providing that the Tapering icon is enabled.



Tapering capability (2)

Lock stitch ON/OFF setting at the beginning/end of stitches.

Number of cycle indication.


Tapering angle mode key.

JANOME MC9450 QCP




Tapering capability (3)

The recommended tapering angle set as default Patterns can also be Mirror imaged Number of pattern repeats can be set 'Tapering angle' and 'cycle (number of repeats)' can be saved in 'save favourite setting'.



Tapering capability (4)

Quick reference and Preview screen are available. This allows you to see the angle of the start and end and also how many pattern repeats.



Ruler Work

Ruler work has been added to the Sewing Applications on page two of the Quilt section.

Adjust the presser foot height to suite the quilt thickness.

For medium to heavy weight quilts, select "Medium". For lighter weight quilts, select "Light".

The Presser foot height can be easily adjusted by pressing

the "+" or "-" key next to the presser foot height icon.






NEW AcuFeed Flex foot (HP2)

This foot provides superior visibility and is great for stitching curves and precise topstitching. As with all the AcuFeed feet it works with the lower feed dogs to achieve a more professional result.

The AcuFeed Flex foot (HP2) must be used with the Professional Grade Needle Plate (HP).



Three Needleplates included

Three needleplates included as standard:-Standard needleplate Straight stitch needleplate HP Professional needleplate.